



HOSTAFORM®

Hostaform® M30RS is an acetal copolymer targeted for extrusion shapes (rod, bar, plate, etc.) free of center porosity in large diameters and thicknesses with improved processing. Chemical abbreviation according to ISO 1043-1: POM. ECO-B: Hostaform® ECO-B is a POM-Copolymer with the same properties and performance as standard grades but produced with sustainability in mind. Using a mass-balance approach, biogenic feedstocks are used to offset the use of fossil-based raw materials and decrease greenhouse gas emissions. The process is audited and certified according to the ISCC Plus mass balance approach.

Product information

Product Information			
Resin Identification	POM		ISO 1043
Part Marking Code	>POM<		ISO 11469
•			
Rheological properties			
Melt volume-flow rate	2.2	cm ³ /10min	ISO 1133
Temperature	190	°C	
Load	2.16	kg	
Moulding shrinkage, parallel	2.2	%	ISO 294-4, 2577
Moulding shrinkage, normal	1.8	%	ISO 294-4, 2577
Typical mechanical properties			
Tensile modulus	2500	MPa	ISO 527-1/-2
Tensile stress at yield, 50mm/min	60	MPa	ISO 527-1/-2
Tensile strain at yield, 50mm/min	12	%	ISO 527-1/-2
Flexural modulus	2400	MPa	ISO 178
Flexural stress at 3.5%	68	MPa	ISO 178
Flexural strain at failure	3.5	%	ISO 178
Compressive stress at 1% strain	26	MPa	ISO 604
Charpy impact strength, 23°C	250	kJ/m²	ISO 179/1eU
Charpy impact strength, -30°C	190	kJ/m²	ISO 179/1eU
Charpy notched impact strength, 23°C		kJ/m²	ISO 179/1eA
Poisson's ratio	0.38 ^[C]		
[C]: Calculated			
Thermal properties			
Melting temperature, 10°C/min	166	°C	ISO 11357-1/-3
Temperature of deflection under load, 1.8 MPa		°C	ISO 75-1/-2
Coefficient of linear thermal expansion		E-6/K	ISO 11359-1/-2
(CLTE), parallel			
Coefficient of linear thermal expansion (CLTE),	120	E-6/K	ISO 11359-1/-2
normal			
Thermal conductivity of melt	0.155	W/(m K)	ISO 22007-2
Specific heat capacity of melt		J/(kg K)	ISO 22007-4
Physical/Other properties			
Humidity absorption, 2mm	0.2	%	Sim. to ISO 62
Water absorption, 2mm	0.75		Sim. to ISO 62
Density		kg/m ³	ISO 1183
··-·· <i>j</i>			.55 1.00

Printed: 2025-05-30 Page: 1 of 6





HOSTAFORM®

Injection

Drying Recommended	no	
Drying Temperature	100	°C
Drying Time, Dehumidified Dryer	3 - 4	h
Processing Moisture Content	≤0.2	%
Melt Temperature Optimum	190	°C
Min. melt temperature	180	°C
Max. melt temperature	200	°C
Screw tangential speed	≤0.3	m/s
Mold Temperature Optimum	100	°C
Min. mould temperature	80	°C
Max. mould temperature	120	°C
Hold pressure range	60 - 120	MPa
Back pressure	4	MPa
Ejection temperature	140	°C

Characteristics

Processing Injection Moulding, Film Extrusion, Extrusion, Sheet Extrusion, Other Extrusion,

Blow Moulding, Calendering, Compression moulding

Delivery form Pellets

Additives Release agent Sustainability Bio-Content

Additional information

Injection molding

Preprocessing

Drying is generally not required because Celcon® and Hostaform® acetal copolymers are not hydroscopic nor are they degraded by moisture during processing. Excessive moisture can lead to splay (silver streaking) in molded parts. For better uniformity in molding especially when using regrind or material that has been stored in containers open to the atmosphere, recommended drying conditions are 80 C (180 F) for 3hours. Desiccant hopper dryers are not required. Maximum water content = 0.35%

Processing

Standard reciprocating screw injection molding machines with a high compression screw (minimum 3:1 and preferably 4:1) and low back pressure (0.35 Mpa/50 PSI) are favored. Using a low compression screw (I.E. general purpose 2:1 compression ratio) can result in unmelted particles and poor melt homogeneity. Using a high back pressure to make up for a low compression ratio may lead to excessive shear heating and deterioration of the material.

Melt Temperature: Preferred range 182-199 C (360-390 F). Melt temperature should never exceed 230 C (450 F).

Mold Surface Temperature: Preferred range 82-93 C (180-200 F) especially with

Printed: 2025-05-30 Page: 2 of 6





HOSTAFORM®

wall thickness less than 1.5 mm (0.060 in.). May require mold temperature as high as 120 C (250 F) to reproduce mold surface or to assure minimal molded in stress. Wall thickness greater than 3mm (1/8 in.) may use a cooler (65 C/150 F) mold surface temperature and wall thickness over 6mm (1/4 in.) may use a cold mold surface down to 25 C (80 F). In general, mold surface temperatures lower than 82 C (180 F) may hinder weld line formation and produce a hazy surface or a surface with flow lines, pits and other included defects that can hinder part performance.

Postprocessing

Postprocessing conditioning and moisturizing are not required. It may be necessary to fixture large or complicated parts with varying wall thickness to prevent warpage while cooling to ambient temperature.

Film extrusion

Preprocessing

Drying is generally not required because Celcon materials are not hydroscopic nor are they degraded by moisture during processing. Excessive moisture can cause surface defects on the extruded film. For better uniformity especially when using regrind or material that has been stored in containers open to the atmosphere, recommended drying conditions are 3 Hrs. at 80 C (180 F). Desiccant hopper dryers are not required. Max. moisture content = 0.35%.

Processing

Standard extruders with a length to diameter ratio of at least 20:1 are recommended. The screw should be a high compression ratio of at least 3:1 and preferably 4:1 to assure good melting and melt homogeneity. The design should be approximately 35% each for feed and metering sections with the remaining 30% as the transition zone.

Melt temperature: 160-220 C (320-430 F)

Postprocessing

Postprocessing conditioning or moisturizing is not required.

Other extrusion

Preprocessing

Drying is generally not required because Celcon materials are not hydroscopic nor are they degraded by moisture during processing. Excessive moisture can cause surface defects. For better uniformity especially when using regrind or material that has been stored in containers open to the atmosphere, recommended drying is 3 hours at 80 C (180 F). Desiccant hopper dryers are not required. Max. moisture content = 0.35%

Processing

Printed: 2025-05-30 Page: 3 of 6





HOSTAFORM®

Standard extruders with a length to diameter ratio of at least 20:1 are recommended. The screw should be a high compression ratio of at least 3:1 and preferably 4:1 to assure good melting and uniform melt homogeneity. The design should be approximately 35% each for the feed and metering sections with the remaining 30% as transition zone.

Melt temperature 180-220 C (355-430F)

Postprocessing

Postprocessing conditioning or moisturizing are not required. For thick walled sections (>3mm or 1/8 in.), annealing is recommended to reduce internal stresses.

Annealing temperature: 130-140 C (265-285 F)

Annealing time: 10 min/mm thickness

Profile extrusion

Preprocessing

Drying is generally not required because Celcon materials are not hydroscopic nor are they degraded by moisture during processing. Excessive moisture can cause surface defects on the extrusion. For better uniformity especially when using regrind or material that has been stored in containers open to the atmosphere, recommended drying conditions are 3 Hrs. at 80 C (180 F). Desiccant hopper dryers are not required. Max. moisture content = 0.035%.

Processing

Standard extruders with a length to diameter ratio of at least 20:1 are recommended. The screw should be a high compression ratio of at least 3:1 and preferably 4:1 to assure good melting and melt homogeneity. The design should be approximately 35% each for feed and metering sections with the remaining 30% as the transition zone.

Melt temperature: 180-220 C (360-430 F).

Postprocessing

Postprocessing or moisturizing is not required. For thick walled extrusions (>3 mm or 1/8 in.), annealing is recommended to reduce internal stresses.

Annealing temperature: 130-140 C (265-285 F)

Annealing time: 10 min/mm thickness

Sheet extrusion

Preprocessing

Drying is generally not required because Celcon materials are not hydroscopic nor are they degraded by moisture during processing. Excessive moisture can lead to surface defects. For better uniformity in sheet extrusion especially when

Printed: 2025-05-30 Page: 4 of 6





HOSTAFORM®

using regrind or material that has been stored in containers open to the atmosphere, recommended drying is 3 hours at 80 C (180 F). Desiccant hopper dryers are not required. Max. water content = 0.35%.

Processing

Standard extruders with a length to diameter ratio of at least 20:1 are recommended. The screw should be a high compression ratio (at least 3:1 and preferably 4:1) to assure good melting and uniform melt homogeneity. The screw design should be approximately 35% each for the feed and metering sections with the remaining 30% as the transition zone.

Melt temperature 180-190 C (355-375 F).

Postprocessing

Postprocessing conditioning or moisturizing is not required. For thick walled sections (>3mm or 1/8 in.), annealing is recommended to reduce internal stresses.

Annealing temperature: 130-140 C (265-285 F)

Annealing time: 10 min/mm wall thickness

Blow molding Preprocessing

Consult product information services.

Processing

Consult product information services.

Postprocessing

Consult product information services.

Calandering Preprocessing

Consult product information services.

Processing

Consult product information services.

Postprocessing

Consult product information services.

Compression molding Preprocessing

Printed: 2025-05-30 Page: 5 of 6

(+) 18816996168 Ponciplastics.com



HOSTAFORM® M30RS ECO-B

Processing

Consult product information services.

Consult product information services.

Postprocessing

Consult product information services.

Processing Notes

Pre-Drying

Drying is not normally required. If material has come in contact with moisture through improper storage or handling or through regrind use, drying may be necessary to prevent splay and odor problems.

Printed: 2025-05-30 Page: 6 of 6

Revised: 2024-11-05 Source: Celanese Materials Database

NOTICE TO USERS: Values shown are based on testing of laboratory test specimens and represent data that fall within the standard range of properties for natural material. These values alone do not represent a sufficient basis for any part design and are not intended for use in establishing maximum, minimum, or ranges of values for specification purposes. Colourants or other additives may cause significant variations in data values. Properties of moulded parts can be influenced by a wide variety of factors including, but not limited to, material selection, additives, part design, processing conditions and environmental exposure. Other than those products expressly identified as medical grade (including by MT® product designation or otherwise), Celanese's products are not intended for use in medical or dental implants. Regardless of any such product designation, any determination of the suitability of a particular material and part design for any use contemplated by the users and the manner of such use is the sole responsibility of the users, who must assure themselves that the material as subsequently processed meets the needs of their particular product or use. To the best of our knowledge, the information contained in this publication is accurate; however, we do not assume any liability whatsoever for the accuracy and completeness of such information. The information contained in this publication should not be construed as a promise or guarantee of specific properties of our products. It is the sole responsibility of the users to investigate whether any existing patents are infringed by the use of the materials mentioned in this publication. Moreover, there is a need to reduce human exposure to many materials to the lowest practical limits in view of possible adverse effects. To the extent that any hazards may have been mentioned in this publication, we neither suggest nor guarantee that such hazards are the only ones that exist. We recommend that persons intending to rely on any recommendation or to use any e

© 2025 Celanese or its affiliates. All rights reserved. Celanese®, registered C-ball design and all other trademarks identified herein with ®, TM, SM, unless otherwise noted, are trademarks of Celanese or its affiliates. Fortron is a registered trademark of Fortron Industries LLC.