

HOSTAFORM® S 4000P CT - POM

Experimental Grade. Please contact your Celanese representative for further information.

Description

Chemical abbreviation according to ISO 1043-1: POM-HI POM copolymer, modified Hostaform® S 4000P CT is an impact-modified acetal copolymer with high flowability for demanding injection molding applications. Hostaform® S 4000P CT has a significantly higher MVR compared to Hostaform® S 27064, with comparable mechanical properties, and is non-hygroscopic in nature. It is recommended for long flow length and/or thin-walled part geometries.

Physical properties	Value	Unit	Test Standard
Density	1370	kg/m ³	ISO 1183
Melt volume rate, MVR	39	cm ³ /10min	ISO 1133
MVR temperature	190	°C	ISO 1133
MVR load	2.16	kg	ISO 1133
Molding shrinkage, parallel	2.0	%	ISO 294-4, 2577
Molding shrinkage, normal	1.9	%	ISO 294-4, 2577
Water absorption, 23°C-sat	0.65	%	ISO 62

Mechanical properties	Value	Unit	Test Standard
Tensile modulus	1600	MPa	ISO 527-2/1A
Tensile stress at yield, 50mm/min	38	MPa	ISO 527-2/1A
Tensile strain at yield, 50mm/min	12	%	ISO 527-2/1A
Charpy notched impact strength, 23°C	8.5	kJ/m ²	ISO 179/1eA

Thermal properties	Value	Unit	Test Standard
Melting temperature, 10°C/min	166	°C	ISO 11357-1/-3

Typical injection moulding processing conditions

Pre Drying	Value	Unit	Test Standard
Necessary low maximum residual moisture content	0.15	%	-
Drying time	3 - 4	h	-
Drying temperature	100 - 120	°C	-
Temperature	Value	Unit	Test Standard
Hopper temperature	20 - 30	°C	-
Feeding zone temperature	60 - 80	°C	-
Zone1 temperature	170 - 180	°C	-
Zone2 temperature	180 - 190	°C	-
Zone3 temperature	190 - 200	°C	-
Zone4 temperature	190 - 200	°C	-
Nozzle temperature	190 - 200	°C	-
Melt temperature	190 - 200	°C	-
Mold temperature	60 - 85	°C	-
Hot runner temperature	190 - 200	°C	-
Pressure	Value	Unit	Test Standard
Back pressure max.	20	bar	-
Speed	Value	Unit	Test Standard
Injection speed	slow-medium	-	-
Screw Speed	Value	Unit	Test Standard
Screw speed diameter, 25mm	150	RPM	-
Screw speed diameter, 40mm	100	RPM	-
Screw speed diameter, 55mm	70	RPM	-

Other text information

Pre-drying

Drying is not normally required. If material has come in contact with moisture through improper storage or handling or through regrind use, drying

HOSTAFORM® S 4000P CT - POM

Experimental Grade. Please contact your Celanese representative for further information.

may be necessary to prevent splay and odor problems.

Longer pre-drying times/storage

The product can then be stored in standard conditions until processed.

Characteristics

Special Characteristics

High flow

Delivery Form

Pellets

Product Categories

Impact modified

Additives

Release agent, Plasticizer

Processing

Injection molding

Contact Information

General Disclaimer

NOTICE TO USERS: Values shown are based on testing of laboratory test specimens and represent data that fall within the standard range of properties for natural material. These values alone do not represent a sufficient basis for any part design and are not intended for use in establishing maximum, minimum, or ranges of values for specification purposes. Colorants or other additives may cause significant variations in data values. Properties of molded parts can be influenced by a wide variety of factors including, but not limited to, material selection, additives, part design, processing conditions and environmental exposure. Any determination of the suitability of a particular material and part design for any use contemplated by the users and the manner of such use is the sole responsibility of the users, who must assure themselves that the material as subsequently processed meets the needs of their particular product or use. To the best of our knowledge, the information contained in this publication is accurate; however, we do not assume any liability whatsoever for the accuracy and completeness of such information. The information contained in this publication should not be construed as a promise or guarantee of specific properties of our products. It is the sole responsibility of the users to investigate whether any existing patents are infringed by the use of the materials mentioned in this publication. Moreover, there is a need to reduce human exposure to many materials to the lowest practical limits in view of possible adverse effects. To the extent that any hazards may have been mentioned in this publication, we neither suggest nor guarantee that such hazards are the only ones that exist. We recommend that persons intending to rely on any recommendation or to use any equipment, processing technique or material mentioned in this publication should satisfy themselves that they can meet all applicable safety and health standards. We strongly recommend that users seek and adhere to the manufacturer's current instructions for handling each material they use, and entrust the handling of such material to adequately trained personnel only. Please call the telephone numbers listed for additional technical information. Call Customer Services for the appropriate Materials Safety Data Sheets (MSDS) before attempting to process our products. The products mentioned herein are not intended for use in medical or dental implants.

Trademark

© 2014 Celanese or its affiliates. All rights reserved. (Published 27.July.2016). Celanese®, registered C-ball design and all other trademarks identified herein with ®, TM, SM, unless otherwise noted, are trademarks of Celanese or its affiliates. Fortron is a registered trademark of Fortron Industries LLC.
