

FORTRON® 0205

Polyphenylene sulfide

0205 is an easy flowing unfilled grade. It demonstrates excellent chemical resistance and thermal stability. Intended for compounding with various fillers. Available standard in pellet (0205P4) and powder 'flake' (0205B4) form.

Product information

Resin Identification	PPS	ISO 1043
Part Marking Code	>PPS<	ISO 11469

Rheological properties

Moulding shrinkage, parallel	1.2 %	ISO 294-4, 2577
Moulding shrinkage, normal	1.5 %	ISO 294-4, 2577

Typical mechanical properties

Tensile modulus	4000 MPa	ISO 527-1/-2
Tensile stress at break, 5mm/min	66 MPa	ISO 527-1/-2
Tensile strain at break, 5mm/min	2 %	ISO 527-1/-2
Flexural modulus	3900 MPa	ISO 178
Flexural strength	130 MPa	ISO 178
Izod notched impact strength, 23 °C	2 kJ/m ²	ISO 180/1A
Izod impact strength, 23 °C	30 kJ/m ²	ISO 180/1U
Hardness, Rockwell, M-scale	95	ISO 2039-2
Poisson's ratio	0.36 ^[C]	

[C]: Calculated

Thermal properties

Melting temperature, 10 °C/min	280 °C	ISO 11357-1/-3
Glass transition temperature, 10 °C/min	90 °C	ISO 11357-1/-3
Temperature of deflection under load, 1.8 MPa	115 °C	ISO 75-1/-2
Temperature of deflection under load, 8 MPa	95 °C	ISO 75-1/-2
Coefficient of linear thermal expansion (CLTE), parallel	53 E-6/K	ISO 11359-1/-2
Coefficient of linear thermal expansion (CLTE), normal	52 E-6/K	ISO 11359-1/-2
Specific heat capacity of melt	1830 J/(kg K)	ISO 22007-4

Electrical properties

Volume resistivity	1E9 Ohm.m	IEC 62631-3-1
Electric strength	17 kV/mm	IEC 60243-1
Comparative tracking index	100	IEC 60112
Arc Resistance	124 s	UL 746B

Physical/Other properties

Water absorption, 2mm	0.02 %	Sim. to ISO 62
Water absorption, Immersion 24h	0.03 %	Sim. to ISO 62
Density	1400 kg/m ³	ISO 1183

FORTRON® 0205

Polyphenylene sulfide

Injection

Drying Recommended	yes
Drying Temperature	110 °C
Drying Time, Dehumidified Dryer	2 - 4 h
Processing Moisture Content	≤0.02 %
Melt Temperature Optimum	315 °C
Min. melt temperature	275 °C
Max. melt temperature	320 °C
Screw tangential speed	0.2 - 0.3 m/s
Mold Temperature Optimum	150 °C
Min. mould temperature	135 °C
Max. mould temperature	160 °C
Hold pressure range	30 - 70 MPa
Back pressure	3 MPa
Ejection temperature	230 °C

Characteristics

Processing	Injection Moulding, Other Extrusion
Delivery form	Pellets, Powder
Special characteristics	Chemical resistant

Additional information

Injection molding

Preprocessing

In spite of the minimum moisture absorption a drying of FORTRON is necessary. Predrying in a dehumidified air dryer at 120 degC/3-4 hours is recommended.

Processing

On injection molding machines with 15-25 D long three-section screws, are usual in the trade, the unreinforced FORTRON is processable. A shut-off nozzle is recommended.

Melt temperature 310-320 degC
Mold wall temperature at least 140 degC

A medium injection rate is normally preferred. All mold cavities must be effectively vented.

Processing Notes

Pre-Drying

FORTRON should in principle be predried. Because of the necessary low maximum residual moisture content the use of dry air dryers is recommended. The dew point should be ≤ - 30° C. The time between drying and processing should be as short as possible.

Storage

FORTRON® 0205

Polyphenylene sulfide

For subsequent storage the material should be stored dry in the dryer until processed (≤ 60 h).

NOTICE TO USERS: Values shown are based on testing of laboratory test specimens and represent data that fall within the standard range of properties for natural material. These values alone do not represent a sufficient basis for any part design and are not intended for use in establishing maximum, minimum, or ranges of values for specification purposes. Colourants or other additives may cause significant variations in data values. Properties of moulded parts can be influenced by a wide variety of factors including, but not limited to, material selection, additives, part design, processing conditions and environmental exposure. Other than those products expressly identified as medical grade (including by MT® product designation or otherwise), Celanese's products are not intended for use in medical or dental implants. Regardless of any such product designation, any determination of the suitability of a particular material and part design for any use contemplated by the users and the manner of such use is the sole responsibility of the users, who must assure themselves that the material as subsequently processed meets the needs of their particular product or use. To the best of our knowledge, the information contained in this publication is accurate; however, we do not assume any liability whatsoever for the accuracy and completeness of such information. The information contained in this publication should not be construed as a promise or guarantee of specific properties of our products. It is the sole responsibility of the users to investigate whether any existing patents are infringed by the use of the materials mentioned in this publication. Moreover, there is a need to reduce human exposure to many materials to the lowest practical limits in view of possible adverse effects. To the extent that any hazards may have been mentioned in this publication, we neither suggest nor guarantee that such hazards are the only ones that exist. We recommend that persons intending to rely on any recommendation or to use any equipment, processing technique or material mentioned in this publication should satisfy themselves that they can meet all applicable safety and health standards. We strongly recommend that users seek and adhere to the manufacturer's current instructions for handling each material they use, and entrust the handling of such material to adequately trained personnel only. Please call the telephone numbers listed for additional technical information. Call Customer Services for the appropriate Materials Safety Data Sheets (MSDS) before attempting to process our products.

© 2025 Celanese or its affiliates. All rights reserved. Celanese®, registered C-ball design and all other trademarks identified herein with ®, TM, SM, unless otherwise noted, are trademarks of Celanese or its affiliates. Fortron is a registered trademark of Fortron Industries LLC.