



## LAPRENE® 83F000833 NEUTRO

## **Product information**

Resin Identification Part Marking Code	SEBS >SEBS<		ISO 1043 ISO 11469
Rheological properties			
Melt mass-flow rate Melt mass-flow rate, Temperature Melt mass-flow rate, Load	190	g/10min °C kg	ISO 1133
Typical mechanical properties			
Tensile stress at 100% elongation Stress at 300% elongation Stress at break Elongation at break, perpendicular Shore A hardness, 3s Compression set, 70°C, 24h Tear strength, normal	2.5 9.5 792 67 48	MPa MPa MPa % kN/m	ISO 527-1/-2 or ISO 37 ISO 527-1/-2 or ISO 37 ISO 527-1/-2 or ISO 37 ISO 527-1/-2 or ISO 37 ISO 48-4 / ISO 868 ISO 815 ISO 34-1
Physical/Other properties			
Density	1220	kg/m <sup>3</sup>	ISO 1183
Injection Drying Recommended Drying Temperature Drying Time, Dehumidified Dryer Melt Temperature Optimum Min. melt temperature Max. melt temperature Screw tangential speed Mold Temperature Optimum Min. mould temperature Max. mould temperature Max. mould temperature	2 180 170 190 ≤15 30 20	°C	
Processing	Injection Moulding		
Additional information Processing Notes	Pre-Drying		

Drying not necessary

## Storage

Laprene must be stored indoors in the original, unopened and undamaged packaging, away from direct sunlight, moisture and heat.

Printed: 2025-05-30





## LAPRENE<sup>®</sup> 83F000833 NEUTRO

Printed: 2025-05-30

Revised: 2024-05-24 Source: Celanese Materials Database

NOTICE TO USERS: Values shown are based on testing of laboratory test specimens and represent data that fall within the standard range of properties for natural material. These values alone do not represent a sufficient basis for any part design and are not intended for use in establishing maximum, minimum, or ranges of values for specification purposes. Colourants or other additives may cause significant variations in data values. Properties of moulded parts can be influenced by a wide variety of factors including, but not limited to, material selection, additives, part design, processing conditions and environmental exposure. Other than those product expressly identified as medical grade (including by MT® product designation or otherwise), Celanese's products are not intended for use in medical or dental implants. Regardless of any such product designation, any determination of the suitability of a particular material and part design for any use contemplated by the users and the manner of such use is the sole responsibility of the users, who must assure themselves that the material as subsequently processed meets the needs of their particular product or use. To the best of our knowledge, the information contained in this publication is accurate; however, we do not assume any liability whatsoever for the accuracy and completeness of such investigate whether any existing patents are infringed by the use of the materials mentioned in this publication. Moreover, there is a need to reduce human exposure to many materials to the lowest practical limits in view of possible adverse effects. To the extent that any hazards may have been mentioned in this publication, we neither suggest nor guarantee that such hazards are the only ones that exist. We recommend that persons intending to rely on any recommendation or to use any equipment, processing technique or material information. Call Customer Services for the appropriate Materials Safety Data Sheets (MSDS) before attempting to process our products.

© 2025 Celanese or its affiliates. All rights reserved. Celanese®, registered C-ball design and all other trademarks identified herein with ®, TM, SM, unless otherwise noted, are trademarks of Celanese or its affiliates. Fortron is a registered trademark of Fortron Industries LLC.

Page: 2 of 2