



SANTOPRENE® 241-80W236

SANTOPRENE®

A soft, colorable, specialty thermoplastic vulcanizate (TPV) in the thermoplastic elastomer (TPE) family. It is designed for use in plumbing applications in contact with potable water. This grade of Santoprene® TPV is shear-dependent and can be processed on conventional thermoplastics equipment for injection molding, extrusion, blow molding, thermoforming or vacuum forming. It is polyolefin based and recyclable within the manufacturing stream.

Key Features

- · Certified by NSF to NSF/ANSI Standard 61: Drinking Water System Components Health Effects.
- · Contains a stabilization system for protection against copper and other metal-catalyzed degradation.

Product information

Resin Identification	TPV	ISO 1043
Part Marking Code	>TPV<	ISO 11469

Typical mechanical properties

Tensile stress at 100% elongation, perpendicular	4.4	MPa	ISO 37
Tensile stress at break, perpendicular	11	MPa	ISO 527-1/-2 or ISO 37
Elongation at break, perpendicular	560	%	ISO 527-1/-2 or ISO 37
Shore A hardness, 15s	87		ISO 48-4 / ISO 868

Physical/Other properties

Density	960 kg/m³	ISO 1183

Injection

Max. regrind level	20 %
Back pressure	0.517 MPa

Extrusion

Drying Temperature	82	°C
Drying Time, Dehumidified Dryer	3	h
Melt Temperature Range	202	°C

Characteristics

Processing Injection Moulding, Multi Injection Moulding, Extrusion, Sheet Extrusion,

Coextrusion, Blow Moulding, Thermoforming

Delivery form Pellets

Additional information

Injection molding Holding pressure should be about 50 to 75% of the actual injection pressure.

A high screw RPM (100 to 200) is recommended.

Back pressure is not always needed, however, a back pressure of 0.3 to 0.7 MPa may be used to ensure a homogeneous melt and maintain a consistent shot size. A higher back pressure is normally employed when using masterbatches.

Processing Notes Processing Notes

Printed: 2025-05-30 Page: 1 of 2

Revised: 2025-04-21 Source: Celanese Materials Database

(+) 18816996168 Ponciplastics.com



SANTOPRENE® 241-80W236

Desiccant drying for 3 hours at 80 °C (180 °F) is recommended. Santoprene® TPV has a wide temperature processing window from 175 to 230 °C (350 to 450 °F) and is incompatible with acetal and PVC.

Printed: 2025-05-30 Page: 2 of 2

Revised: 2025-04-21 Source: Celanese Materials Database

NOTICE TO USERS: Values shown are based on testing of laboratory test specimens and represent data that fall within the standard range of properties for natural material. These values alone do not represent a sufficient basis for any part design and are not intended for use in establishing maximum, minimum, or ranges of values for specification purposes. Colourants or other additives may cause significant variations in data values. Properties of moulded parts can be influenced by a wide variety of factors including, but not limited to, material selection, additives, part design, processing conditions and environmental exposure. Other than those products expressly identified as medical grade (including by MT® product designation or otherwise), Celanese's products are not intended for use in medical or dental implants. Regardless of any such product designation, any determination of the suitability of a particular material and part design for any use contemplated by the users and the manner of such use is the sole responsibility of the users, who must assure themselves that the material as subsequently processed meets the needs of their particular product or use. To the best of our knowledge, the information contained in this publication is accurate; however, we do not assume any liability whatsoever for the accuracy and completeness of such information. The information contained in this publication should not be construed as a promise or guarantee of specific properties of our products. It is the sole responsibility of the users to investigate whether any existing patents are infringed by the use of the materials mentioned in this publication. Moreover, there is a need to reduce human exposure to many materials to the lowest practical limits in view of possible adverse effects. To the extent that any hazards may have been mentioned in this publication, we neither suggest nor guarantee that such hazards are the only ones that exist. We recommend that persons intending to rely on any recommendation or to use any e

© 2025 Celanese or its affiliates. All rights reserved. Celanese®, registered C-ball design and all other trademarks identified herein with ®, TM, SM, unless otherwise noted, are trademarks of Celanese or its affiliates. Fortron is a registered trademark of Fortron Industries LLC.